

Straight Blade Devices

15A, 125V, 2 Pole, 3 Wire Grounding

Load:Logic[®] Load Control Receptacles

Features

- Designed for Automatic Receptacle (plug load) Control
- Half controlled face and downstream control
- Low voltage wire control
- Tamper Resistant... NOT Plug Resistant[®]

Ordering Information

| Description | Device Color | UPC Number | Catalog Number |
|----------------------------|--------------|--------------|----------------|
| Decorator face, back wired | Green | 783585428413 | HBL5262LC1GN |

Listings

cULus 498B SA UL File No. E481574
Fed. Spec. WC596G
Complies with:NEC Section 406.3 (E), ASHRAE 90.1 Section 8.4.2,California Title 24
Artcile 130.5(d)
NEMA WD-6 Compliant

Specifications

| | |
|------------------------|-----------------------------------|
| Face | Nylon |
| Base | Nylon |
| Power Contacts | 0.031in (0.8) Brass |
| Wire Clamp | 0.062in (1.6) Steel-Nickel Finish |
| Mounting Strap | 0.047in (1.2) Brass |
| Terminal Screws | #8-32 Brass, Multiple Drive |
| Self -Grounding Staple | Stainless Steel |
| Mounting Screws | Zinc-Plated Steel |

Performance


Electrical
Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 2,000V minimum

Mechanical
Product Identification Ratings are a permanent part of the device
Terminal Accomodation #14-10 AWG stranded or solid copper conductor only
Terminal Identification Terminals identified in accordance with UL498 and CSA (Brass, White, Green)

Environmental
Flammabilty UL94V-2
Operating Location Indoor Use Only
Operating Temperature 0° to 40°C (32° to 104°F) Relative Humidity (non-condensing) 0% to 95% (w/o impact)

HUBBELL



Complementary Products

Wallplate, Decorator Opening, Stainless Steel SS26

Online Resources

Customer Use Drawing
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

