

## Straight Blade Devices

15A, 125V, 2 Pole, 3 Wire Grounding

## Load:Logic® Load Control Receptacles

### Features

- Designed for Automatic Receptacle (plug load) Control
- Half controlled face and downstream control
- Clear Connect/Vive Enabled wireless control
- Tamper Resistant... NOT Plug Resistant®

### Ordering Information

Description	Device Color	UPC Number	Catalog Number
Decorator face, back wired	Gray	783585530697	HBL5262RFC1GY

### Listings

cULus 498B SA UL File No. E481574  
Fed. Spec. WC596G  
Complies with: NEC Section 406.3 (E), ASHRAE 90.1 Section 8.4.2, California Title 24  
Article 130.5(d)  
NEMA WD-6 Compliant

### Specifications

Face	Nylon
Base	Nylon
Power Contacts	0.031in (0.8) Brass
Wire Clamp	0.062in (1.6) Steel-Nickel Finish
Mounting Strap	0.047in (1.2) Brass
Terminal Screws	#8-32 Brass, Multiple Drive
Self -Grounding Staple	Stainless Steel
Mounting Screws	Zinc-Plated Steel

### Performance


**Electrical**  
Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 2,000V minimum

**Mechanical**  
Product Identification Ratings are a permanent part of the device  
Terminal Accomodation #14-10 AWG stranded or solid copper conductor only  
Terminal Identification Terminals identified in accordance with UL498 and CSA (Brass, White, Green)

**Environmental**  
Flammabilty UL94V-2  
Operating Location Indoor Use Only  
Operating Temperature 0° to 40°C (32° to 104°F) Relative Humidity (non-condensing) 0% to 95% (w/o impact)

# HUBBELL



### Complementary Products

Wallplate, Decorator Opening, Nylon	NP26GY
Wallplate, Decorator Opening, Stainless Steel	SS26

### Online Resources

Customer Use Drawing  
eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

