

Straight Blade Devices 15A, 125V, 2 Pole, 3 Wire Grounding Flanged Receptacles

HUBBELL

Features

- Stainless steel flange
- Covered terminal screws

Ordering Information

Description	Device Color	UPC	Catalog Number
Stainless steel flange, brown phenolic body, covered terminals	Brown	783585013367	HBL5279

Listings

UL Listed, File E2186
Certified to CSA, C22.2, No. 42
NEMA® WD-6 Compliant

Specifications

Face	Phenolic
Power Contacts	.040" (1.0) Brass
Terminal Screw	#8-32 Brass, Multiple Drive
Mounting Screw	Nickel plated brass

Performance

Electrical


Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

Mechanical

Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid wire only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA

Environmental

Flammability	UL 94 V-0
Operating Temperatures	Maximum continuous 75°C; minimum -40°C (w/o impact)



Resources

Customer Use Drawing
eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

