

## Straight Blade Devices

15A 125V, 2 Pole, 3 Wire Grounding

## Special Combination Duplex Receptacles

# HUBBELL

### Ordering Information

Description	Device Color	UPC Number	Catalog Number
Ivory nylon face, 2 circuit, back and side wired	Ivory	783585435428	HBL5292I

### Listings

Certified to CSA, C22.2, No. 42 file 285  
UL Listed to UL498 File E2186

### Specifications

Face	Nylon
Base	Reinforced PET
Face Style	Finder Groove

### Performance

#### Electrical

Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

#### Mechanical

Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA

#### Environmental

Flammability	UL 94 V-2 or better
Operating Temperatures	Maximum continuous 75°C; minimum -40°C (w/o impact)



### Complementary Products

Wallplate or Weatherproof Cover      Duplex Opening

### Online Resources

eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

