

Straight Blade Devices  
15A 125V/15A 250V, 2 Pole, 3 Wire Grounding  
Special Combination Duplex Receptacles

# HUBBELL

## Ordering Information

Description	Device Color	UPC	Catalog Number
Brown nylon face, 2 circuit, back and side wired	Brown	783585435404	HBL5292

## Listings

UL Listed to UL498 File E2186  
Certified to CSA, C22.2, No. 42 file 285

## Specifications

Face	Nylon
Base	Reinforced PET
Power Contacts	.037" (.9) Brass

## Performance

### Electrical

Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

### Mechanical

Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA

### Environmental

Flammability	UL 94 V-2 or better
Operating Temperatures	Maximum continuous 75°C; minimum -40°C (w/o impact)



## Accessories

Wallplate or Weatherproof Cover Duplex Opening

## Resources

eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

