

IEC Pin and Sleeve

30A, 3 PhaseY 347/600V AC, 4 Pole, 5 Wire

Mechanical Interlock

Features

- Replaceable spring-loaded receptacle liftcover with gasket
- Plug-Check™ mechanism to detect the presence of plug

Ordering Information

| Description | UPC | Catalog Number |
|--|--------------|----------------|
| Pin and Sleeve fused circuit-lock interlock device | 783585406107 | HBL530MIF5W |

Color code
Black

Standards

UL Listed for US and Canada
CSA certified

Specifications

| | |
|------------------|----------|
| Base and Top | Valox® |
| Handle | Valox® |
| Enclosure Gasket | Neoprene |
| Shaft | Brass |
| Shaft Seal | Neoprene |

Performance

| | |
|----------------------|--|
| Electrical | |
| Current Interrupting | Certified for current interrupting at full rated current and voltage |
| Dielectric Voltage | Withstands 3,000V AC Min |
| Max Working Voltage | 600V AC |

Mechanical

| | |
|-------------------------|--|
| Impact Resistance | In accordance with UL 746C |
| Mounting | External adjustment feet |
| Terminal Identification | In accordance with UL, CSA and international conventions |


Environmental

| | |
|------------------------|--|
| Flammability | UL94-5VA and V-0 Classification |
| Ingress Protection | IP66 Suitability |
| Operating Temperatures | Max. Continuous +75°C; Min. Continuous -40°C |
| UV Resistance | All materials are UV stabilized |

Online Resources

Customer Use Drawing
eCatalog
Installation Instructions

HUBBELL



Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

