

SpikeShield® Power Quality Products
20A, 125V AC, 2 Pole, 3 Wire Grounding
Surge Protection Receptacles

HUBBELL

Features

- Automatic self-grounding staple
- Distinctive surge symbol provides quick identification
- Power-on indicator light verifies that power is available
- Alert alarm sounds when surge protection is no longer functioning

Ordering Information

Description	Device Color	UPC	Catalog Number
Surge Protective Devices, Straight Blade Receptacle, Duplex	White	783585219899	HBL5360WSA



Listings

UL Listed File E2186
 Listed to UL Standards 498
 CSA Certified to Specification C22.2 No. 42

Specifications

Face Material	Nylon
Base Material	Nylon
Power Contact	.031" (.8) Brass
Contact Design	Tandem Modified Bypass
Mounting Strap	.050" (1.3) Steel-Zinc Coated


Performance

Electrical

Protection Modes	Normal and Common Modes
Response Time	Approximately 5 ns
Transient Suppression Voltage	Peak Energy (10 X 100 µs), Peak Current (8 X 20 µs) 120V AC + 10% - 15%

Environmental

Flammability	UL 94V-2
Operating Temperature	32°F to 140°F (0°C to 60°C)



Online Resources

Customer Use Drawing
 eCatalog
 Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

