

Straight Blade Devices
20A, 125V, 2 Pole, 3 Wire Grounding
Special Combination Duplex Receptacles

HUBBELL

Ordering Information

Description	Device Color	UPC	Catalog Number
Brown nylon, side and	Brown	783585014746	HBL5392

Listings

UL Listed to UL498 File E2186
Certified to CSA, C22.2, No. 42 file 285

Specifications

Face	Nylon
Base	Reinforced PET
Power Contacts	.037" (.9) Brass

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current
Dielectric Voltage Withstands 2,000V minimum

Mechanical

Product Identification Ratings are a permanent part of the device
Terminal Accommodation #14-#10 AWG copper stranded or solid conductor only
Terminal Identification Terminals identified in accordance with UL 498 and CSA

Environmental

Flammability UL 94 V-2 or better
Operating Temperatures Maximum continuous 75°C; minimum -40°C (w/o impact)



Online Resources

[eCatalog](#)

Accessories

[Wallplate or Weatherproof Cover](#)

[Duplex Opening](#)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

