

Watertight Devices

30A, 3 Phase 480V AC, 3 Pole, 4 Wire

Twist-Lock® Receptacle

Features

- Impact resistant PBT lid, cover plate, and receptacle body
- Thermoplastic elastomer seal
- Stainless steel hardware and corrosion-resistant connection points

Ordering Information

Description	Device Color	UPC Number	Catalog Number
Thermoplastic elastomer black receptacle	Black	783585511283	HBL69W76BK

Listings

IP69K rating
Listed to UL498
Certified to CSA C22.2 No. 42
Meets NEMA WD-1, WD-6 and ANSI standards
UL Listed, CSA Certified to Type 4, 4X, 12, 6, 6P

Specifications

Body	PBT
Contact Carrier	White Nylon
Terminal Retainer	Clear polycarbonate
Contacts	Nickel plated brass
Core	White Nylon
Terminal Screws	Nickel plated brass
Hardware	Stainless Steel
Electrical	Current Interrupting
Rated for current interruption per UL498	Electrical


Performance

Dielectric Voltage 3500V AC	Electrical
Max Working Voltage As marked	Electrical
Moisture Resistance UL Listed 4, 4X, 12, 6, 6P	Environmental
Operating temperatures -40°C (without impact) to +60°C continuous	Environmental
Temperature Rise 30°C max per UL498 at rated current	Environmental

UV resistance

All exposed materials are UV stabilized

HUBBELL



Complementary Products

Watertight Plug	HBL28W76BK
-----------------	------------

Online Resources

eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

