

Hospital Products

Power Strips

Heavy Duty Relocatable Power Taps

HUBBELL

Features

- Heavy-duty 18 gauge galvanized steel housing with durable powder coat finish
- All models come with built in circuit breaker for over current protection
- Tamper-Resistant Receptacles



Ordering Information

Description	Color	Catalog No.	UPC
Relocatable Power Taps, 20A 125V, 6 Outlet, 15' Cord	Black	HBL6RPT1520BK	783585452548

Listings

cULus Listed UL1363 RPT

Specifications

Electrical

Current	20A
Voltage	125V
Frequency	60Hz
Over Current Protection	20A CB

Physical

Length	11.12" (282.4)
Width	2.22" (56.4)
Height	1.6" (40.5)

Environmental

Operating Temperature	-40°F to 160°F (-40°C to 70°C)
-----------------------	--------------------------------

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484 Phone (800) 288-6000 • Fax (800) 255-1031
Specifications subject to change without notice.

