

Straight Blade Devices  
 20A, 3 Phase Y 120/208V AC, 4 Pole, 4 Wire  
 Non-Grounding  
 Plug

# HUBBELL

## Features

- Industrial heavy duty plug
- Angled, low profile
- 4-position assembly

## Ordering Information

Description	Cord Diameter	UPC	Catalog Number
Plug, nylon, angle, 4-position	.390"-.775"(9.9-19.7)	783585013282	HBL7251C

## Listings

UL Listed to UL498 File E1706  
 NEMA® WD-6 Compliant

## Specifications

Housing/Cord Clamp	Nylon
Blade Holder	Nylon
Terminal Retainer	Clear Polycarbonate
Blades	Brass
Terminal Screws	Brass
Terminal Clamp	Nickel plated steel
Assembly Screws	Zinc plated steel

## Performance

### Electrical


Current Interrupting Certified for current interrupting at full rated current  
 Dielectric Voltage Withstands 2,000V minimum

### Mechanical

Cord Accomodation .390"-.775"(9.9-19.7)  
 Terminal Accommodation #14-10 AWG. Standed copper wire only  
 Terminal Identification Terminals identified in accordance with UL 498 and CSA

### Environmental

Flammability UL 94 V-2  
 IP Suitability IP20  
 Operating Temperatures Maximum continuous 75°C; minimum -40°C (w/o impact)



## Resources

Customer Use Drawing  
 eCatalog