

# Non-NEMA Twist-Lock® Devices 20A, 125/250V, 3 Pole, 3 Wire Non-Grounding Corrosion Resistant Insulgrip® Plug

# HUBBELL

## Features

- Nickel plated blades and stainless steel screws provide maximum corrosion resistance.
- Ribbed nylon housing provides a secure grip and impact and chemical resistance.
- Superior cord grip design protects terminations from excess strain.
- Integral dust shield protects wiring chamber from dust or contaminants.

## Ordering Information

Description	Cord Diameter	UPC	Catalog Number
Corrosion resistant, yellow nylon.	.360"-.930" (9-24)	783585037646	HBL99CM65C



## Listings

Listed to UL 498  
Fed.Spec. W-C-596  
Certified to CSA C22.2 No.42

## Specifications

Housing / Cord Clamp	Nylon
Terminal Retainer	Clear polycarbonate
Blades	Nickel Plated Brass
Terminal Screws	#10-32 Bronze (Phillips / Slotted / Robertson)
Terminal Clamp	Cold rolled steel – nickel plated
Assembly Screws	Stainless Steel

## Performance

### Electrical

Current Interrupting Certified for current interrupting at full rated current  
Dielectric Voltage Withstands 2,000V minimum

### Mechanical

Terminal Accommodation #16 AWG - #8 AWG stranded copper wire only.

Terminal Identification Terminals identified in accordance with UL 498

### Environmental

Flammability HB or better per UL94 or CSA 22.2 No. 0.6  
Moisture Resistance IP20 Suitability  
Operating Temperatures Maximum Continuous 75°C Minimum -40°C (w/o impact)

## Accessories

Connector	HBL73CM14C
Single Receptacle	HBL7310B
Flanged Receptacle	HBL3326C
Weatherproof Boot	HBL60CM31

## Resources

eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

