

## Switched Disconnects and Enclosures

### Circuit-Lock® 30A Disconnects with LED Indicators

### Suitable as Motor Disconnects

#### Features

- Six highly visible integral phase identification LEDs for use on 3 Phase Y system
- LEDs provide secondary means of visual confirmation of make/break on all phases
- Cover cannot be removed with switch in the “ON” position
- Verification of opening of load side contacts
- Highly visible red handle can be locked in the OFF position as a method of compliance with OSHA Lockout/Tagout requirements

#### Ordering Information

Description	UPC Number	Catalog Number
Disconnect with Jog switch and LEDs, Non-Metallic	783585365145	HBLDS3PJ

#### Listings

cULus Listed  
NSF Certified and IP69K Rating

#### Specifications

Base and Top	PBT
Handle	PBT
Conduit Hub	¾ in. Zinc
Enclosure Gasket	Neoprene
Frame	Galvanized Steel
Enclosure Screws	Stainless Steel 300 Series
Shaft (Unfused)	PBT
Shaft Seal	Molded Neoprene

#### Performance

Electrical	
Current Interrupting	Certified for current interrupting at full rated current and voltage
Dielectric Voltage	Withstands 3000V AC minimum
Max. Working Voltage	600V AC RMS
Short Circuit Current Ratings (SCCR): (Motor Disconnect)	Suitable for use on a circuit capable of delivering not more than 65kA RMS symmetrical, 600V AC max. when protected by Class J fuses rated 30A max.


#### Mechanical

Impact Resistance	In accordance with UL 746C
Mounting	External fully adjustable feet
Terminal Identification	In accordance with UL, CSA and international conventions

#### Environmental

Flammability	UL94-5VA and V0 Classification
Moisture Resistance	Indoor and Outdoor – Type 4X (Wash down, Corrosion resistant); Indoor – Type 12 (Dust-tight, Falling Dirt, Noncorrosive Liquids).
Operating Temperature	Max. Continuous: 75°C; Min. Continuous: -40°C without impact
UV Resistance	All materials are UV stabilized

# HUBBELL



#### Complementary Products

Replacement Cover	HBLDS3RCPJ
Replacement Ground Block	HBL30RGB
Replacement Neutral Block	HBL30RNB
Replacement Switches	HBLDS3RS
Replacement Mounting Feet	HBLRFT1

#### Online Resources

Customer Use Drawing  
eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

