

Temporary Power
Temporary Industrial Lighting
Fluorescent Light String

HUBBELL

Features

- Inline on/off switch for ease of operation
- 120V AC electronic ballast protected by light fixture

Ordering Information

Description	UPC	Catalog Number
Fluorescent light string, 34.5" single fixture w/ hanging straps	783585467450	HBLFS5035

Listings

UL
CSA
ETL

Specifications

Light Type	Fluorescent
Plug Type	NEMA 5-15P
Length	34.25
Width	2.625

Performance

Electrical	
Lamp Life	14,000
Light Color	4100 K
Lumen Output	3750
Rating	15A 125V
Wattage	50

Mechanical	
Cord Length	6 ft.
Cord Type	16 AWG SJTOW



Online Resources

[eCatalog](#)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

