

Temporary Power  
Temporary Industrial Lighting  
LED Stringer Lights

# HUBBELL

## Features

- Inline on/off switch for ease of operation
- Extra durable polycarbonate outer tube
- Diffuser protects user's eyes from bright light

## Ordering Information

Description	UPC	Catalog Number
28W High power LED light string with in line on/off switch	783585467283	HBLLS2834



## Listings

UL  
CSA  
ETL

## Online Resources

[eCatalog](#)

## Specifications

Light Type	LED
Plug Type	NEMA 5-15P
Length	34.25
Width	2.625

## Performance

### Electrical

Lamp Life	50000
Light Angle Degree	130
Light Color	4700-5200 K
Lumen Output	2928
Rating	15A 125V
Watts	28

### Mechanical

Cord Length	6 ft.
Cord Type	16 AWG SJTOW

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

