

Temporary Power
Temporary Industrial Lighting
Metal Halide Worklights

HUBBELL

Features

- Ballast is detachable and portable
- Frame made of 12 gauge steel tube providing impact resistance while in use and for transporting
- Heavy duty telescoping mast

Ordering Information

Description	UPC	Catalog Number
5 -10 ft. metal halide cart light with portable detachable ballast	783585528151	HBLMH1000



Online Resources

[eCatalog](#)

Listings

UL
CSA
ETL

Specifications

Light Type	Halide
Height Range	5-10 ft.
Weight	120 lbs
Ballast	Portable/Detachable

Performance

Electrical

Cool down time	5-15 minutes
Lamp Life	10,000 hrs
Lumen Output	110000
Rating	15A 125V
Warm-up time	4-5 minutes
Watts	1000

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

