

Temporary Power
Temporary Industrial Lighting
Metal Halide Worklights

HUBBELL

Features

- 2 lights providing double the lumen output
- Frame made of 12 gauge steel tube providing impact resistance while in use and for transporting
- Heavy duty telescoping mast which is raised and lowered by self-breaking winch

Ordering Information

Description	UPC	Catalog Number
6 -12 ft. metal halide cart light	783585528168	HBLMH2000



Listings

UL
CSA
ETL

Online Resources

[eCatalog](#)

Specifications

Light Type	Halide
Height Range	6-12 ft.
Weight	196 lbs
Ballast	Fixed

Performance

Electrical	
Cool down time	5-15 minutes
Lamp Life	10,000 hrs
Lumen Output	220000
Rating	15A 125V
Warm-up time	4-5 minutes
Watts	2000

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

