

Temporary Power  
Temporary Industrial Lighting  
Metal Halide Worklights

# HUBBELL

## Features

- Compact size for easy handling
- Durable formed and welded wire guard
- Hook with mounting feature mounts in seconds

## Ordering Information

Description	UPC	Catalog Number
High bay metal halide light with wire guard	783585528175	HBLMH400



## Online Resources

[eCatalog](#)

## Listings

[UL](#)

## Specifications

Light Type	Halide
Lamp	Type P-Pulse Start, O-rated
Ballast	Multi tap

## Performance

<b>Electrical</b>	
Lumen Output	29000
Rating	15A 125V
Watts	400

<b>Mechanical</b>	
Cord Length	3 ft.

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

