

Features

- Preconfigured for quick plug and play
- Wireless mesh network communication
- Utilizes standard NEMA configurations



Ordering Information

Description	UPC Number	Catalog Number
SMART POWER CABLE, L21-30, 3 phase Y NEMA DEV	78358556935	HBLRG302121

Complementary Products

Ethernet Gateway

Listings

UL - end effectors only

Online Resources

eCatalog

Specifications

Antenna	Fully enclosed
Enclosure material	High impact resistant Lexan
Measurements	V, A, W, Wh, VA, Hz, Pf
Accuracy	+/- 1.0%
Input Voltage	277/480V AC
Current range	30A
Circuit Type	3 phase Y
Wireless protocol	Self configuring, load balancing mesh network
Typical Transmission range	Up to 30 meters
Encryption	AES 128-bit

Performance

Electrical

Power consumption .6W

Environmental

Operating humidity 5 to 95% non-condensing

Operating temperature 32 to 104F (0 to 40C)

20 to 167F (7 to 75C)