

### Features

- Preconfigured for quick plug and play
- Wireless mesh network communication
- Utilizes standard IEC configurations

### Ordering Information

Description	UPC Number	Catalog Number
SMART POWER CABLE, PS, IEC, 30/32A, 240/415	78358556936	HBLRG32532W



### Listings

UL - end effectors only

### Specifications

Antenna	Fully enclosed
Enclosure material	High impact resistant Lexan
Measurements	V, A, W, Wh, VA, Hz, Pf
Accuracy	+/- 1.0%
Input Voltage	100-480V AC
Current range	30/32A
Circuit Type	3 phase
Wireless protocol	Self configuring, load balancing mesh network
Typical Transmission range	Up to 30 meters
Encryption	AES 128-bit

### Performance

#### Electrical

Power consumption .6W

#### Environmental

Operating humidity 5 to 95% non-condensing

Operating temperature 32 to 104F (0 to 40C)

20 to 167F (7 to 75C)

### Complementary Products

Ethernet Gateway

### Online Resources

eCatalog