

Temporary Power
Temporary Industrial Lighting
Fluorescent Maintenance Worklights

HUBBELL

Features

- Soft end caps provide moisture resistance and impact protection
- Polycarbonate outer tube is extremely durable
- 25' cord is oil-resistant and water tight

Ordering Information

| | | |
|-----------------------------------|--------------|----------------|
| Description | UPC | Catalog Number |
| Fluorescent work light, 45 in. | 783585467443 | HBLWL2525 |

Listings

UL
CSA
ETL

Specifications

| | |
|---------------------|--|
| Outer Tube Material | Polycarbonate |
| Light Type | Fluorescent |
| Plug Type | NEMA 5-15P |
| Length | 45 |
| Width | 1.75 |
| Included | 2 Horizontal plastic hangers, 1 attached metal hanging Hook |
| Replacement Bulb | 5000-2011 (Not sold by Hubbell) |

Performance

Electrical

| | |
|--------------|--------------|
| Lamp Life | 20,000 hours |
| Light Color | 2125 K |
| Lumen Output | 2125 |
| Rating | 15A 125V |
| Wattage | 25 |

Mechanical

| | |
|-------------|------------|
| Cord Length | 25 ft. |
| Cord Type | 16/3 SJTOW |



Online Resources

[eCatalog](#)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

