

Temporary Power Temporary Industrial Lighting Hazardous Location Lights

HUBBELL

Features

- Rated for use in Class 1, Div 1, Groups C & D locations & Class 2, Div 1, Groups F & G locations
- Inline transformer can be placed outside hazardous zone while light is used inside zone and still remain code compliant
- Housing is made of corrosion resistant, lightweight, highly durable material.

Ordering Information

Description	UPC	Catalog Number
Fluorescent, Class 1, Div 1 Groups C & D, Class 2, Div 1 Groups F & G, 12V, inline transformer	783585467290	HBLXF6012V



Listings

UL
CSA
ETL

Online Resources

[eCatalog](#)

Specifications

Light Type	Fluorescent
Plug Type	No Plug
Length	23.5
Width	4

Performance

Electrical

Inline Transformer	12V
Lamp Life	14,000 hours
Light Color	4100 K
Wattage	26

Mechanical

Cord Length	60 ft.
Cord Type	16/3 SOW

Environmental

Explosion Proof	Class 1, Div 1 Groups C & D, Class 2, Div 1 Groups F & G
-----------------	--

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

