Wire Basket Tray Tray Section Overhead Tray, 118" Length



Features

- · For use in control environments
- · Top rail T-weld construction prevent snags
- · Flat shaped cross wire provides more cable support area



Ordering Information

Standards

UL Classified as equipment grounding conductor ASTM A 641

Specifications

Material	100% Recycled Steel
Finish	Pre-Galvanized
Flat Shaped Cross-Wires	Cable Support Area03125 square inch
Mesh Spacing	2" x 4" (50.5 x 101.6)

Performance

No-Splice Support Spacing	5' (1524)
Splice Kit Qty- 90 Degree Sweep Elbow	6
Splice Kit Qty- Straight Splice	4
Support Spacing	6' (1828.8)
Tray Area (cu. in.)	24
Weight Capacity (lb/ft)	58

Dimensions- inches (mm)

 Height	2" (51)	
Width	12" (305)	
Length	118" (2997.2)	
	()	

Accessories

Angled Cutting Tool	HBTCUTTOOL
Splice Kit	HBTSK
Corner Splice	HBTCS
Pre-Galvanized Steel Cover	HBTCVR12
Pre-Galvanized Steel Divider	HBTDIV2

Online Resources

eCatalog

