

Wire Basket Tray Tray Section Overhead Tray, 118" Length


HUBBELL

Features

- For use in control environments
- Top rail T-weld construction prevent snags
- 5mm round wire minimum

Ordering Information

| Height | Width | Catalog Number | UPC Number |
|--------|-------|------------------|--------------|
| 2" | 30" | HBT0230BK | 783585416373 |



Standards

UL/cUL Classified as equipment grounding conductor
ASTM A 641

Specifications

| | |
|--------------|-------------------------------|
| Material | 100% Recycled Steel |
| Color | Black |
| Paint | Polyester TGIC Powder Coating |
| Ground Point | Masked for bonding |
| Mesh Spacing | 2" x 4" (50.5 x 101.6) |

Performance

| | |
|---------------------------------------|-------------|
| No-Splice Support Spacing | 5' (1524) |
| Splice Kit Qty- 90 Degree Sweep Elbow | 15 |
| Splice Kit Qty- Straight Splice | 6 |
| Support Spacing | 6' (1828.8) |
| Tray Area (cu. in.) | 60 |
| Weight Capacity (lb/ft) | 70 |

Dimensions- inches (mm)

| | |
|--------|---------------|
| Height | 2" (51) |
| Width | 30" (762) |
| Length | 118" (2997.2) |

Accessories

| | |
|---------------------|-------------------|
| Angled Cutting Tool | HBTCUTTOOL |
| Splice Kit | HBTSKBK |
| Corner Splice | HBTCSBK |
| Black Steel Divider | HBTDIV2BK |

Online Resources

eCatalog

