


# Wire Basket Tray Tray Section Overhead Tray, 118" Length

# HUBBELL

## Features

- For use in control environments
- Top rail T-weld construction prevent snags
- 5mm round wire minimum



## Ordering Information

Height	Width	Catalog Number	UPC Number
4"	12"	<b>HBT0412BK</b>	783585416755

## Standards

UL/cUL Classified as equipment grounding conductor  
ASTM A 641

## Specifications

Material	100% Recycled Steel
Color	Black
Paint	Polyester TGIC Powder Coating
Ground Point	Masked for bonding
Mesh Spacing	2" x 4" (50.5 x 101.6)

## Performance

No-Splice Support Spacing	5' (1524)
Splice Kit Qty- 90 Degree Sweep Elbow	6
Splice Kit Qty- Straight Splice	6
Support Spacing	6' (1828.8)
Tray Area (cu. in.)	48
Weight Capacity (lb/ft)	78

## Dimensions- inches (mm)

Height	4" (102)
Width	12" (305)
Length	118" (2997.2)

## Accessories

Angled Cutting Tool	<b>HBTCUTTOOL</b>
Splice Kit	<b>HBTSKBK</b>
Corner Splice	<b>HBTCGBK</b>
Black Steel Cover	<b>HBTCVR12BK</b>
Black Steel Divider	<b>HBTDIV4BK</b>

## Online Resources

eCatalog