

Straight Blade Devices

20A, 125V, 2 Pole, 3 Wire Grounding

HBL[®] Extra Heavy Duty MAX Specification Grade Single Receptacle

HUBBELL

Features

- Weather-resistance complies with national electrical code requirements
- Triangle marking on face indicates isolated ground
- Finder Groove Face
- Back wired ground terminal allows faster, easier installation

Ordering Information

| Description | Device Color | UPC Number | Catalog Number |
|------------------------------------|--------------|--------------|----------------|
| Weather-Resistant, Isolated ground | Orange | 783585320489 | IG5361WR |

Listings

UL Listed to UL498 File No. E2186
Certified to CSA 22.2, No. 42 File 285
Fed. Spec. W-C-604
NEMA[®] WD-6 Compliant

Specifications


| | |
|--------------------------|---------------------|
| Face | Nylon |
| Base | PBT |
| Power Contacts | .037 in. (.9) Brass |
| Ground Contacts | Brass |
| Mounting Strap | .050" (1.3) Brass |
| Auto Self-grounding Clip | Stainless steel |
| Mounting Screws | Zinc plated steel |

Performance

| | |
|-------------------------|--|
| Electrical | |
| Current Interrupting | Certified for current interrupting at full rated current |
| Dielectric Voltage | Withstands 2,000V minimum |
| Mechanical | |
| Product Identification | Ratings are a permanent part of the device |
| Terminal Accommodation | #12-#10 AWG copper stranded or solid conductor only |
| Terminal Identification | Terminals identified in accordance with UL 498 and CSA |
| Environmental | |
| Flammability | Top: UL 94V-2, Base: UL 94V-0 |
| Operating Temperatures | Maximum continuous 75°C; minimum -40°C (w/o impact) |



20A 125V
NEMA 5-20R
UL CSA
1 HP



Complementary Products

Wallplate or Weatherproof Cover 1.40" Opening

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

