

**Straight Blade Devices**  
**20A, 250V, 2 Pole, 3 Wire Grounding**  
**Heavy Duty Specification Grade Single Receptacle**

# HUBBELL

**Features**

- Triangle marking on face indicates isolated ground
- Patented bypass contact design

**Ordering Information**

Description	Device Color	UPC	Catalog Number
Single, Isolated	Orange	783585880501	IG5461

**Listings**

UL Listed to UL498 File No. E2186  
 Certified to CSA 22.2, No. 42 File 285  
 NEMA® WD-6 Compliant  
 NEMA® WD-6 Compliant

**Specifications**


Face	Nylon
Base	PBT
Power Contacts	.037 in. (.9) Brass
Ground Contact	Brass
Clamp	Nickel plated brass
Terminal Screws	Plated brass
Mounting Strap	.050 in. (1.3) Brass
Automatic Self-grounding Clip	Stainless steel
Mounting Screws	Stainless steel

**Performance**

<b>Electrical</b>	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum
<b>Mechanical</b>	
Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA
<b>Environmental</b>	
Flammability	Top: UL 94V-2, Base: UL 94V-0
Operating Temperatures	Maximum continuous 75°C; minimum -40°C (w/o impact)



**20A 250V**  
**NEMA 6-20R**  
 UL CSA  
 2 HP



**Online Resources**

- Customer Use Drawing
- eCatalog
- Installation Instructions

**Accessories**

Wallplate or Weatherproof Cover

1.40" Opening

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

