Straight Blade Devices 30A, 250V, 2 Pole, 3 Wire Grounding Single Receptacle

HUBBELL

Features

- Sequenced contacts assure protection
- Catalog number, ratings and certifications molded in face
- One piece design power and ground contacts

Ordering Information

Description Device Color UPC Catalog Number Receptacle, orange, Orange 783585880754 IG9330 isolated ground

Listings

UL Listed File E2186 CSA Certified NEMA® WD-6 Compliant

Specifications

Housing Reinforced Thermoplastic Polyester

Mounting Plate .062 in. (1.5) Pre-Plated Steel

Contacts Brass

Ground Shunt Brass

Box Terminals Copper

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 2,000V minimum

Mechanical

Product Identification Ratings are a permanent part of the device Terminal Accommodation #12 AWG through #4 AWG copper wire only


Terminal Identification Terminals identified in accordance with UL 498 and CSA

Environmental

Flammability UL 94 V-0 IP Suitability IP20

Operating Temperatures Maximum continuous 75°C; minimum -40°C (w/o impact)





Accessories

Wallplate or Weatherproof Cover 2.16" Opening

Resources

Customer Use Drawing eCatalog

