

## IEC Pin and Sleeve

### Watertight Devices

## Receptacle/Connector Replacement Interior

# HUBBELL

### Features

- Sequential contact engagement

### Ordering Information

| Description  | UPC          | Catalog Number |
|--|--------------|----------------|
| Pin and Sleeve Replacement Interior, For 4W 60A, IEC | 783585420448 | IN460DF        |

### Device Color

Black



### Standards

UL Listed  
CSA Certified

### Specifications

|                 |                       |
|-----------------|-----------------------|
| Gaskets         | Neoprene              |
| Hinge Spring    | Stainless Steel       |
| Contact Carrier | High-Impact Thermoset |
| Terminal Screws | Stainless Steel       |
| Assembly Screws | Stainless Steel       |

### Performance

#### Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 3,000V AC  
Max Working Voltage 600V AC RMS

#### Mechanical

Impact Resistance In accordance with UL746C  
Product Identification Ratings are a part of the external label and molded into the receptacle mount  
Terminal Identification Terminals identified in accordance with North American and International conventions

#### Environmental

Flammability UL94-5VA and V-0 classification  
Ingress Protection IP67 Suitability  
Operating Temperatures Max. Continuous:75°C; Min. Continuous:-40°C w/o impact

### Online Resources

eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

