IEC Pin and Sleeve

100A, 3 PhaseY, 120/208V, 4 Pole, 5 Wire

HUBBELL

Corrosion Resistant Watertight Receptacle

Features

- UL Type 4X, 12 and IP69k environmental ratings
- Super tough insulated non-metallic housing
- Self-closing gasketed cover
- Sequential contact engagement to prevent a momentary over-voltage
- Market leading UL witnessed HP ratings



Ordering Information

Description Watertight IEC Pin and Sleeve Receptacle

UPC 783585510057

PBT

Catalog Number M5100Ř9

Listings

UL Listed, File E146032

UL Classified to IEC 60309-1 IEC 60309-2

Specifications

Housing Closure Covers

PBT Sealing Gasket

Gaskets Santoprene Terminal Screws

Solid Neoprene Retainer **High-Impact Thermoset**

Stainless Steel

Performance

Electrical

Certified for current interrupting at full rated Current Interrupting

current

Dielectric Voltage Withstand 3000V AC

Max. Working Voltage 600V RMS

Mechanical

Impact Resistance Per CSA C22.2 No. 182.1 / UL1682

Product Identification Identification and ratings are a permanent part of

the device housing

Terminal Identification Terminals identified in accordance with North

American and IEC conventions

Environmental

V-0 Flammability

Ingress Protection Type 3R,3RX,4X AND IP68,IP69K

Moisture Resistance IEC 60309-1

Operating Temperatures Maximum Continuous 75°C; Minimum - 40°C

w/o impact

Complementary Products

Cover Assemblies

Online Resources

Customer Sales Drawing

eCatalog

Installation Instructions





