

# Fire-Rated Poke-Throughs Multi-Service Painted Pedestal 3 Inch Core Hole Unit

# HUBBELL®

## Features

- 1–4 hour fire rating  
(1–3 hour for steel floor units and concrete topping, D900 Series Design)
- For 2 1/4 in. to 7 in. floor thickness
- Approved for use in the City of Chicago

## Ordering Information

| Description  | UPC          | Catalog Number |
|--|--------------|----------------|
| Large Capacity Multi-Service Pedestal Through-Floor Fitting with (1) 1 1/4 in. EMT stem for low voltage and (1) 1/2 in. EMT stem for power applications. | 783585204475 | PT7XC          |

## Listings

cULus Listed  
Fire Resistance - R8429  
Outlet Box- E31999

## Specifications

|          |           |
|----------|-----------|
| Material | Composite |
|----------|-----------|

## Electrical

|                            |  |
|----------------------------|--|
| Power Wiring Capacity      | Up to ten #12 AWG type THHN wires, or Up to six #12 AWG and two #10 AWG type THHN wires                      |
| Voice/Data Wiring Capacity | Up to four 25 pair tel./data cables (200 #22 AWG tel./data conductors), or Up to five IBM Type 2 data cables |

## Mechanical

|                         |  |
|-------------------------|--|
| Max. Cu Cross Section   | 1/2" Power EMT .0461 sq. in., 1 1/2" Low Voltage EMT .1000 sq. in.                           |
| UL Spacing Restrictions | Min. of 2 ft. O.C. and not more than one unit per each 65 sq. ft. of floor area in each span |

## Related Product

|                                 |                 |
|---------------------------------|-----------------|
| Pedestal Service Fitting        | <b>FR80AL</b>   |
| 6-Gang Pedestal Service Fitting | <b>FR680GYA</b> |
| 4-Gang Pedestal Service Fitting | <b>FR480GYA</b> |
| 2-Gang Pedestal Service Fitting | <b>FR280GYA</b> |



## Links

[ecatalog](#)  
[Media](#)

