

AV In-Wall Enclosure
2-Gang
Recessed TR AV Plastic Box


HUBBELL

Features

- Easily mounts to studs
- Allows for multiple options for AV in-wall solutions


Ordering Information

Description	Device Color	UPC	Catalog Number
Smooth face	Blue	88377830586	RR1500



Listings

CSA Certified 22.2, No. 42
 UL Listed to UL 514C



Specifications

Box	Thermoplastic
Nails	2 1/2 inch galvanized steel
Volume	21 cubic in. (344 cubic cm)

Accessories

Recessed TR Duplex Receptacle with Cable Pass Thru	RR1512
Recessed TR Duplex Receptacle with Snapfit Openings	RR1514

Performance

Environmental

Flammability	UL 94 V-2
Operating Temperatures	Maximum continuous 75°C; minimum -40°C (w/o impact)

Online Resources

Customer Use Drawing
 eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

