

## Fire-Rated Poke-Throughs

### 10" SystemOne Series

#### Kit

# HUBBELL

#### Features

- (1) S1R10PTFIT fitting and (1) S1R10CVRBRS Brass Plated Recessed Cover
- (2) S1R10PSPREPBRKT Perimeter Brackets
- (4) S1R10CBFPT Center Feed Thru,(3) S1R10PBFBLANK Perimeter Blank Bottom Plate, and (1) S1R10PBF075 Perimeter 3/4" EMT Bottom Feed Plates
- (1) S1R10CENTERDIV Center and (1) S1R10PERIMDIV Perimeter Dividers

#### Ordering Information

| Description  | UPC Number   | Catalog Number |
|--|--------------|----------------|
| SystemOne, 10" Series, Kit, Includes S1R10PTFIT, S1R10CVRBRS, S1R10PSPREPBRKT, S1R10CBFPT, S1R10PBFBLANK, S1R10PBF075, S1R10CENTERDIV, S1R10PERIMDIV | 783585548227 | S1R10PTBRS     |



#### Listings


cULus Listed as Fittings and Outlet Boxes, also Classified for Fire Resistance  
ULC Listed as Fittings and Outlet Boxes for Service Penetration  
UL Scrub Water Compliant  
ADA Compliant

#### Specifications

|  |                                    |
|--|------------------------------------|
| Cover Material                                     | Cast Aluminum                      |
| Cover Finish                                       | Brushed Brass Plated               |
| S1R10PTFIT Fitting Materials                       | Pre-Galvanized Steel & Intumescent |
| Material- Bottom Feed Plates and Metallic Dividers | Pre-Galvanized Steel               |
| Maximum Copper Cross Section- Center Chamber       | 0.0978 sq. in.                     |
| Maximum Copper Cross Section- Perimeter Chamber    | 0.0408 sq. in.                     |

#### Performance

|                                      |   |
|--------------------------------------|---|
| Cover Connection Type                | Recessed  |
| Cover Load Rating                    | 1,000 lbs Static Load Through 3" Diameter Mandrel |
| Drilled or Formed Concrete Hole Size | 10.00" to 10.12"                                  |
| Fire Rating                          | 1-2 Hour rated                                    |
| Minimum Concrete Floor Thickness     | 2.25" (57.2)                                      |



#### Complementary Products

|                              |                 |
|------------------------------|-----------------|
| Pre-Pour Tube                | S1R10PPT        |
| Egress Door Brushes          | S1R10CVRBRUSH   |
| Center Sub-Plates            | S1R10CSP Series |
| Perimeter Sub-Plates         | S1R10PSP Series |
| Center Bottom Feed Plates    | S1R10CBF Series |
| Perimeter Bottom Feed Plates | S1R10PBF Series |

#### Online Resources

Customer Use Drawing  
eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

