

## Fire-Rated Poke-Throughs

### 10" SystemOne Series

#### Kit

# HUBBELL

#### Features

- (1) S1R10PTFIT fitting and (1) S1R10CVRNKL Satin Nickel Plated Recessed Cover
- (2) S1R10PSPZ PreWired Duplex with Leads and (2) S1R10PSPREPBRKT Perimeter Brackets
- (4) S1R10CBFPT Center Feed Thru, (3) S1R10PBFBLANK Perimeter Blank Bottom Plate, and (1) S1R10PBF075 Perimeter 3/4" EMT Bottom Feed Plates
- (1) S1R10CENTERDIV Center and (1) S1R10PERIMDIV Perimeter Dividers

#### Ordering Information

Description	UPC Number	Catalog Number
SystemOne, 10" Series, Kit, Includes S1R10PTFIT, S1R10CVRNKL, S1R10PSPZ, S1R10PSPREPBRKT, S1R10CBFPT, S1R10PBFBLANK, S1R10PBF075, S1R10CENTERDIV, S1R10PERIMDIV	783585548302	S1R10PTZMKL

#### Listings


cULus Listed as Fittings and Outlet Boxes, also Classified for Fire Resistance  
ULC Listed as Fittings and Outlet Boxes for Service Penetration  
UL Scrub Water Compliant  
ADA Compliant

#### Specifications

Cover Material	Cast Aluminum
Cover Finish	Satin Nickel Plated
S1R10PTFIT Fitting Materials	Pre-Galvanized Steel & Intumescent
Material- Bottom Feed Plates and Metallic Dividers	Pre-Galvanized Steel
Sub-Plates and Brackets	Pre-Galvanized Steel- White Painted
Maximum Copper Cross Section- Center Chamber	0.0978 sq. in.
Maximum Copper Cross Section- Perimeter Chamber	0.0408 sq. in.

#### Performance

Cover Load Rating	1,000 lbs Static Load Through 3" Diameter Mandrel
Drilled or Formed Concrete Hole Size	10.00" to 10.12"
Fire Rating	1-2 Hour rated
Minimum Concrete Floor Thickness	2.25" (57.2)



#### Complementary Products

Pre-Pour Tube	S1R10PPT
Egress Door Brushes	S1R10CVRBRUSH
Center Sub-Plates	S1R10CSP Series
Perimeter Sub-Plates	S1R10PSP Series
Center Bottom Feed Plates	S1R10CBF Series
Perimeter Bottom Feed Plates	S1R10PBF Series

#### Online Resources

Customer Use Drawing  
eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

