

# Straight Blade Devices 20A, 125V, 2 Pole, 3 Wire Grounding Straight and Right Angle Pigtailed Terminal

# HUBBELL

## Features

- Transparent housing to inspect contacts
- Audible SNAP, indicates solid connection
- Reduces installation time
- Fully insulated design

## Ordering Information

Description	Wire Type	UPC	Catalog Number
Right angle, orange terminal with 6-inch leads, Isolated Ground, assembled in USA	Solid	783585231211	SNAP1RIG

## Listings

UL Listed to UL498 File No. E2186  
Certified to CSA, C22.2, No. 42 File 285  
Fed. Spec. W-C-596

## Specifications

Contact	Brass
Terminal Body	PBT
Wire	#12 AWG, T90 Nylon FT-1, PVC 90°C (min)

## Performance

### Electrical

Current Interrupting	Receptacle certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

### Mechanical

Terminal Identification	Terminal Wire Leads- Identified in accordance with UL 498
-------------------------	-----------------------------------------------------------

### Environmental

Flammability	UL 94V-2
Operating Temperatures	Maximum continuous 75°C; minimum -40°C (w/o impact)



## Accessories

Mating Receptacle	Hubbell SNAPConnect® Receptacle
-------------------	---------------------------------

## Resources

[eCatalog](#)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

