

## Straight Blade Devices

15 Amp, 125 Volt, 2-Pole, 3-Wire

## SNAPConnect® Permanently Marked Receptacle

# HUBBELL

### Features

- Audible SNAP, indicates solid connection
- Reduces installation time
- Split Circuit, Half Controlled
- Power symbol is clearly visible

### Ordering Information

| Description                                | Device Color | UPC Number   | Catalog Number |
|--|--------------|--------------|----------------|
| One Controlled Face, Split Circuit Hot Tab | Black        | 783585555010 | SNAP5262C1BK   |

### Listings

UL Listed to UL498 File No. E2364  
Certified to CSA, C22.2, No. 42 File 463  
Fed. Spec. W-C-774  
NEMA® WD-6 Compliant

### Specifications

|                |       |
|----------------|-------|
| Face           | Nylon |
| Base           | Nylon |
| Line Contact   | Brass |
| Ground Contact | Brass |

### Performance

#### Electrical

|                      |  |
|----------------------|--|
| Current Interrupting | Certified for current interrupting at full rated current |
| Dielectric Voltage   | Withstands 2,000V minimum                                |

#### Mechanical

|                        |  |
|------------------------|--|
| Product Identification | Ratings are a permanent part of the device |
|------------------------|--|

#### Environmental

|                       |   |
|-----------------------|---|
| Flammability          | UL 94V-2  |
| Operating Temperature | Maximum continuous 75°C; minimum -40°C (without impact) |



### Complementary Products

Wallplate or Weatherproof Cover  
Opening

### Online Resources

eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

