

Straight Blade Devices
20A, 125V, 2 Pole, 3 Wire Grounding
Acceptor® Hazardous Location Plugs

HUBBELL

Ordering Information

Description	Device Color	UPC	Catalog Number
Explosion and dust ignition proof, Male Plug, Single Pack	Metallic	783585412405	UGP20231



Listings

Listed to UL Standard 498

Resources

[eCatalog](#)

Performance

Electrical

Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

Mechanical

Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA

Environmental

Flammability	UL 94 HB or better
Operating Temperatures	Maximum continuous 75°C; minimum -40°C (w/o impact)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

