

## Straight Blade Devices

15A, 125V, 2 Pole, 3 Wire Grounding

## USB Charger Receptacles

### Features

- Weather and Tamper Resistant Commercial Grade
- Two Type C USB Ports
- High Power 5 Amp, 5 Volt USB Output
- USB Ports Rated 10,000 Cycles
- Heavy Duty Spec Grade

### Ordering Information

Description	Color	UPC Number	Catalog Number
Weather and Tamper Resistant 15A/125V Duplex, 5 Amp, 5 Volts USB Ports	Gray		USB15C5GYWR

### Listings

cULus Listed to UL498, UL1310  
Complies with battery charging specification USB BC1.2  
Compatible with USB 1.1/2.0/3.0 devices, including Apple® products  
Meets Section 406.9 of the NEC making it suitable for outdoor use.


### Specifications

Code Compliance	Complies with Part 15 of the FCC Rules
Electrical Ratings	15 or 20 Amp, 125V AC
Port Rating	5 Amp, 5 Volt
Indicator	Green LED
Contacts	Brass Triple-Wipe
Terminal Screws	Stainless Steel
Mounting Strap	Brass
Mounting Screws	Stainless Steel
USB Port	Stainless Steel
Auto-Ground Staple	Stainless Steel

### Performance

<b>Electrical</b>	
Current Interrupting	Certified at full rated current
Dielectric Voltage	Withstands 1,500V minimum
<b>Mechanical</b>	
Operating Temperature	Maximum continuous 75°C, minimum -40°C (w/o impact)
Outdoor Suitability	UL 746C f1
USB Ports	Stainless steel, rated for 10,000 charge-cable insertion cycles
<b>Environmental</b>	
Flammability	UL 94V-2
Outdoor Suitability	UL 746C f1, Weather Resistant Device suitable for use outdoor with 3R extra duty protected enclosure, in compliance with NEC 406.9

# HUBBELL



15A WEATHER RESISTANT (WR) DEVICE

### Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

