# Straight Blade Devices 125V, 2 Pole, 3 Wire Grounding **USB Charger Outlets**

# HUBBELL

#### **Features**

- Four USB ports 5 Amp, 2 Type A and 2 Type-C USB, 5V DC, class 2.0
- Fast charge enabled modulates up to 9 volts
- Switch activated port door; when open enables power; when closed, all power is switched off, for a "zero" no-load draw
- Green LED indicator to show USB power available
- Compatible with USB 1.1/2.0/3.0 devices, including Apple® products

#### **Ordering Information**

**Device Color** UPC Catalog Number Description USB Charger 4 Port Black 883778308949 **USB4ACBK** Outlet. 2 Type A, 2 Type-C USB Ports. 5 Amp, up to 9 Volt DC, Style Line Decorator

## Listings

FCC Approved

Compatible with USB 1.1/2.0/3.0 Devices

# **Specifications**

Face Reinforced Thermoplastic Reinforced Thermoplastic Base I FD Green Indicator Mounting Strap Galvanized steel Auto Self-grounding staple Stainless steel Mounting Screws Zinc plated steel **Terminal Screws** Plated steel **USB Port** Stainless Steel

### **Performance**

**Electrical** 

**Current Interrupting** Receptacle certified for current interrupting at full rated

current

Dielectric Voltage Withstands 1,500V minimum

Mechanical

Product Identification Ratings are a permanent part of the device

#14-#10 AWG copper stranded or solid conductor only **Terminal Accommodation** Terminal Identification Terminals identified in accordance with UL 498 and CSA **USB Port** 

Stainless steel Rated for 10,000 plug insertions and

removal

**Environmental** 

Flammability UL 94V-2

Operating Temperature Maximum continuous 75°C; minimum -40°C (w/o impact)



#### Resources

Installation Instructions Sales Drawing eCatalog

