# Straight Blade Devices 125V, 2 Pole, 3 Wire Grounding **USB** Charger Outlets



## **Features**

- Four USB ports 5 Amp, 2 Type A and 2 Type-C USB, 5V DC, class 2.0
- Fast charge enabled modulates up to 9 volts
- Switch activated port door; when open enables power; when closed, all power is switched off, for a "zero" no-load draw
- Green LED indicator to show USB power available

**Device Color** 

White

Compatible with USB 1.1/2.0/3.0 devices, including Apple® products

UPC

## **Ordering Information**

Description USB Charger 4 Port Outlet. 2 Type A, 2 Type-C USB Ports. 5 Amp, up to 9 Volt DC, Style Line Decorator

**Catalog Number** 883778308987 USB4ACW

## Listings

cULus FCC Approved Compatible with USB 1.1/2.0/3.0 Devices

## **Specifications**

•	
Face	Reinforced Thermoplastic
Base	Reinforced Thermoplastic
LED	Green Indicator
Mounting Strap	Galvanized steel
Auto Self-grounding staple	Stainless steel
Mounting Screws	Zinc plated steel
Terminal Screws	Plated steel
USB Port	Stainless Steel

## Performance

Electrical

**Current Interrupting** Receptacle certified for current interrupting at full rated current **Dielectric Voltage** Withstands 1,500V minimum

### Mechanical

Flammability

Product Identification **Terminal Accommodation Terminal Identification** USB Port

removal Environmental UL 94V-2

Ratings are a permanent part of the device

#14-#10 AWG copper stranded or solid conductor only

Stainless steel Rated for 10,000 plug insertions and

Terminals identified in accordance with UL 498 and CSA

**Operating Temperature** Maximum continuous 75°C; minimum -40°C (w/o impact)



## Resources

Installation Instructions Sales Drawing eCatalog



Wiring Device-Kellems