# Straight Blade Devices 20A, 125V, 2 Pole, 3 Wire Grounding Hospital Grade USB Charger Receptacles Features

- High Power 5 Amp, 5 Volt USB Output
- Combination Ports, One Type A, One Type C
- Tamper Resistant Hospital Grade Duplex Compatible
- USB Ports Rated 10,000 Cycles

## **Ordering Information**

DescriptionColorHopstial Grade, TamperIvoryResistant 20A/125V Duplex,5 Amp, 5 Volts USB Ports

UPC Number Catalog Number 883778307379 USB8300AC5I

### Listings

cULus Listed to UL498, UL1310


### **Specifications**

Face Base LED Contacts Clamp Terminal Screws Mounting Strap Mounting Screws USB Port RTP RTP Green Indicator Plated Steel Plated Steel Idted Steel .040" Zinc Plated Steel Zinc Plated Steel Stainless Steel









20A HOSPITAL GRADE DEVICE

### **Online Resources**

eCatalog

### Performance

# Electrical Certified for current inturrupting at full rated current Dielectric Voltage Withstands 2,000V minimum<br/>Complies with USB BC1.2 Battery Charging and 3.0<br/>Power Delivery Specifications Mechanical Ratings are a permanent part of the device<br/>#14-#10 AWG copper stranded or solid conductor

Terminal Identification

USB Ports

### **Environmental** Flammability Operating Temperature

Ratings are a permanent part of the device #14.#10 AWG copper stranded or solid conductor only Terminals identified in accordance with UL 498 and CSA Stainless steel rated for 10,000 plug incertions and removal

UL 94V-2 re Maximum continuous 75°C, minimum -40°C (w/o impact)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484 Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.



**Wiring Device-Kellems**