

WRD602418SSFSN4

by Wiegmann

Catalog ID: WRD602418SSFSN4



NEMA 4X ^{* Representative image} 1-Door Freestanding
Enclosure with Removable Pin Hinge
and 3-Point Handle 60X24X18 304
Stainless Steel

Designed to protect electrical components and instruments in typical industrial environments. Removable hinge pins reduce time and effort while removing enclosure doors, allowing access to internal components.

- Body and door are fabricated from 304 stainless steel
- Heavy-Duty 316 Stainless Steel Removable Hinge
- Seams are continuously welded and ground smooth
- 3-point keylocking/padlocking combo handle
- Doors are sealed with a poured in place gasket

Product Details

General

Finish Type	Grained Stainless Steel
Material	Stainless Steel
Mounting Type	Freestanding
Number of Doors (Fixed)	1
Series	Removable Pin Hinge
Type	Enclosure
UPC	786725888832

Dimensions

Actual Depth	18.13 in
Actual Height	60.13 in
Actual Width	24.13 in
Cubic Capacity	25920 cu.in
Depth	18
Height	60 in
Weight	219 lb
Width	24 in

Certifications and Compliance

Certified Listed	UL
Nema Rating	3R, 4, 4X, 12 and IP66

```
$(document).on('click', '[data-toggle="lightbox"]', function(event) { event.preventDefault();
$(this).ekkoLightbox();});
```