

by Wiegmann

Catalog ID: WRD723018SSFSN4



NEMA 4X <sup>\*Representative image</sup> 1-Door Freestanding  
Enclosure with Removable Pin Hinge  
and 3-Point Handle 72X30X18 304  
Stainless Steel

Designed to protect electrical components and instruments in typical industrial environments. Removable hinge pins reduce time and effort while removing enclosure doors, allowing access to internal components.

- Body and door are fabricated from 304 stainless steel
- Heavy-Duty 316 Stainless Steel Removable Hinge
- Seams are continuously welded and ground smooth
- 3-point keylocking/padlocking combo handle
- Doors are sealed with a poured in place gasket

# Product Details

---

## General

Finish Type	Grained Stainless Steel
Material	Stainless Steel
Mounting Type	Freestanding
Number of Doors (Fixed)	1
Series	Removable Pin Hinge
Type	Enclosure
UPC	786725888870

## Dimensions

Actual Depth	18.13 in
Actual Height	72.13 in
Actual Width	30.13 in
Cubic Capacity	38880 cu.in
Depth	18
Height	72 in
Weight	284 lb
Width	30 in

## Certifications and Compliance

Certified Listed	UL
Nema Rating	3R, 4, 4X, 12 and IP66

```
$(document).on('click', '[data-toggle="lightbox"]', function(event) { event.preventDefault();
$(this).ekkoLightbox();});
```