

by Wiegmann

Catalog ID: WRD727218SSFSDN4



* Representative image.
NEMA 4X 2-Door Freestanding
Enclosure with Removable Pin Hinge
and 3-Point Handle 72X72X18 304
Stainless Steel

Designed to protect electrical components and instruments in typical industrial environments. Removable hinge pins reduce time and effort while removing enclosure doors, allowing access to internal components.

- Body and doors are fabricated from 304 stainless steel
- Heavy-Duty 316 Stainless Steel Removable Hinge
- Seams are continuously welded and ground smooth
- 3-point keylocking/padlocking combo handle
- Doors are sealed with a poured in place gasket

Product Details

General

Finish Type	Grained Stainless Steel
Material	Stainless Steel
Mounting Type	Freestanding
Number of Doors (Fixed)	2
Series	Removable Pin Hinge
Type	Enclosure
UPC	786725889037

Dimensions

Actual Depth	18.13 in
Actual Height	72.13 in
Actual Width	72.13 in
Cubic Capacity	93312 cu.in
Depth	18
Height	72 in
Weight	522 lb
Width	72 in

Certifications and Compliance

Certified Listed	UL
Nema Rating	3R, 4, 4X, 12 and IP66

\$(document).on('click', '[data-toggle="lightbox"]', function(event) { event.preventDefault();
\$(this).ekkoLightbox(); });