

by Wiegmann

Catalog ID: WRD72XM7724FSD4



* Representative image
NEMA 4 2-Door Freestanding
Removable Pin Hinge Disconnect
72X77.7X24 Carbon Steel - Gray

Designed to protect electrical components and instruments in typical industrial environments. Removable hinge pins reduce time and effort while removing enclosure doors, allowing access to internal components.

- Body and door are fabricated from carbon steel
- Heavy-Duty 316 Stainless Steel Removable Hinge
- Seams are continuously welded and ground smooth. 3-point keylocking/padlocking combo handle
- Doors are sealed with a poured in place gasket. Back panels are included with this enclosure

Product Details

General

Color	Gray
Finish Type	Polyester Powder
Material	Carbon Steel
Mounting Type	Freestanding
Number of Doors (Fixed)	2
Series	Removable Pin Hinge
Type	Disconnect
UPC	786725889181

Dimensions

Actual Depth	24.13 in
Actual Height	72.13 in
Actual Width	77.75 in
Cubic Capacity	133056 cu.in
Depth	24 in
Height	72 in
Weight	787 lb
Width	77 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• cULus• IEC 60950• IP66
Nema Rating	3R, 4, 12 and IP66

```
$(document).on('click', '[data-toggle="lightbox"]', function(event) { event.preventDefault();  
$(this).ekkoLightbox(); });
```