

by Wiegmann

Catalog ID: WRD902420SSFSN4



* Representative image
NEMA 4X 1-Door Freestanding
Enclosure with Removable Pin Hinge
with 3-Point Handle 90X24X20 304
Stainless Steel

Designed to protect electrical components and instruments in typical industrial environments. Removable hinge pins reduce time and effort while removing enclosure doors, allowing access to internal components.

- Body and door are fabricated from 304 stainless steel
- Heavy-Duty 316 Stainless Steel Removable Hinge
- Seams are continuously welded and ground smooth
- 3-point keylocking/padlocking combo handle
- Doors are sealed with a poured in place gasket

Product Details

General

Finish Type	Grained Stainless Steel
Material	Stainless Steel
Mounting Type	Freestanding
Number of Doors (Fixed)	1
Series	Removable Pin Hinge
Type	Enclosure
UPC	786725888931

Dimensions

Actual Depth	20.13 in
Actual Height	90.13 in
Actual Width	24.13 in
Cubic Capacity	43200 cu.in
Depth	20
Height	90 in
Weight	316 lb
Width	24 in

Certifications and Compliance

Certified Listed	UL
Nema Rating	3R, 4, 4X, 12 and IP66

\$(document).on('click', '[data-toggle="lightbox"]', function(event) { event.preventDefault(); \$(this).ekkoLightbox(); });