

by Wiegmann

Catalog ID: WRD903636SSFSN4



\* Representative image  
NEMA 4X 1-Door Freestanding  
Enclosure with Removable Pin Hinge  
and 3-Point Handle 90X36X36 304  
Stainless Steel

Designed to protect electrical components and instruments in typical industrial environments. Removable hinge pins reduce time and effort while removing enclosure doors, allowing access to internal components.

- Body and door are fabricated from 304 stainless steel
- Heavy-Duty 316 Stainless Steel Removable Hinge
- Seams are continuously welded and ground smooth
- 3-point keylocking/padlocking combo handle
- Doors are sealed with a poured in place gasket

## Product Details

---

### General

Finish Type	Grained Stainless Steel
Material	Stainless Steel
Mounting Type	Freestanding
Number of Doors (Fixed)	1
Series	Removable Pin Hinge
Type	Enclosure
UPC	786725888962

### Dimensions

Actual Depth	36.13 in
Actual Height	90.13 in
Actual Width	36.13 in
Cubic Capacity	116640 cu.in
Depth	36
Height	90 in
Weight	534 lb
Width	36 in

### Certifications and Compliance

Certified Listed	UL
Nema Rating	3R, 4, 4X, 12 and IP66

\$(document).on('click', '[data-toggle="lightbox"]', function(event) { event.preventDefault(); \$(this).ekkoLightbox(); });