

by Wiegmann

Catalog ID: WRD907224SSFSDN4



* Representative image.
NEMA 4X 2-Door Freestanding
Enclosure with Removable Pin Hinge
and 3-Point Handle 90X72X24 304
Stainless Steel

Designed to protect electrical components and instruments in typical industrial environments. Removable hinge pins reduce time and effort while removing enclosure doors, allowing access to internal components.

- Body and doors are fabricated from 304 stainless steel
- Heavy-Duty 316 Stainless Steel Removable Hinge
- Seams are continuously welded and ground smooth
- 3-point keylocking/padlocking combo handle
- Doors are sealed with a poured in place gasket

Product Details

General

Finish Type	Grained Stainless Steel
Material	Stainless Steel
Mounting Type	Freestanding
Number of Doors (Fixed)	2
Series	Removable Pin Hinge
Type	Enclosure
UPC	786725889075

Dimensions

Actual Depth	24.13 in
Actual Height	90.13 in
Actual Width	72.13 in
Cubic Capacity	155520 cu.in
Depth	24
Height	90 in
Weight	689 lb
Width	72 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">cULusIEC 60950IP66
Nema Rating	3R, 4, 4X, 12 and IP66

```
$(document).on('click', '[data-toggle="lightbox"]', function(event) { event.preventDefault();  
$(this).ekkoLightbox(); });
```