

by Wiegmann

Catalog ID: WRD90XM3924FS4



\* Representative image  
NEMA 4 1-Door Freestanding  
Removable Pin Hinge Disconnect  
90X39.5X24 Carbon Steel - Gray

Designed to protect electrical components and instruments in typical industrial environments. Removable hinge pins reduce time and effort while removing enclosure doors, allowing access to internal components.

- Body and door are fabricated from carbon steel
- Heavy-Duty 316 Stainless Steel Removable Hinge
- Seams are continuously welded and ground smooth. 3-point keylocking/padlocking combo handle
- Doors are sealed with a poured in place gasket. Back panels are included with this enclosure

# Product Details

---

## General

Color	Gray
Finish Type	Polyester Powder
Material	Carbon Steel
Mounting Type	Freestanding
Number of Doors (Fixed)	1
Series	Removable Pin Hinge
Type	Disconnect
UPC	786725889143

## Dimensions

Actual Depth	24.13 in
Actual Height	90.13 in
Actual Width	39.38 in
Cubic Capacity	84240 cu.in
Depth	24 in
Height	90 in
Weight	536 lb
Width	39 in

## Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"><li>cULus</li><li>IEC 60950</li><li>IP66</li></ul>
Nema Rating	3R, 4, 12 and IP66

```
$(document).on('click', '[data-toggle="lightbox"]', function(event) { event.preventDefault();  
$(this).ekkoLightbox(); });
```