

Aluminum Service Pole

Length of 10'2"

Ivory finish

HUBBELL

Features

- Ceiling trim mounting plate and scuff boot included
- All conductors are #12 AWG stranded copper
- Ready for quick installation
- UL Listed

Ordering Information

Style	Length & Color	UPC Number	Catalog Number
(1) 20A GFCI Duplex, (2) 20A Ground Fault Protected Duplex	10'2", Ivory finish	783585483948	HBLPP10GFI

Listings

UL Listed

Specifications

Length	10'2"
Color/Finish	Ivory finish
Circuits	1 Circuit
Scuff Boot	Included
Ceiling Trim plate	Included
Divider	Included
Length	10'2" (3100)
Width	2.13" (54)
Depth	2.1" (54)



Related Products

Adjustable T-bar bracket	ATB
Replacement trim kit	PPTRIM1

Online Resources

Customer Sales Drawings
Delivery Systems Guide
eCatalog
Installation Instructions
Service Poles Guide

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

